



## PRODUCT DESCRIPTION

Tflex™ CR350 is a soft, compliant, high thermal conductivity, two-part dispensable gap filler providing a low thermal resistance and high reliability.

This dispensable gap filler minimizes stress on components during assembly while providing the reliability of a traditional thermal pad. Tflex™ CR350 is ideal for application where large gap tolerances are present, meeting vertical shock and vibrate requirements, typical of the automotive industry.

The 1:1 mix is easily dispensable through a wide variety of off the shelf dispensing equipment. It is an A+B putty material that cures in place after dispensing and mixing to perfectly fill the gap. The experts at Laird can help design the system that is right for you.

## FEATURES AND BENEFITS

- Thermal Conductivity 3.6W/mK
- Dispensable and Compliant
- Minimizes stress during assembly while maintaining reliability through a wide range of environmental conditions
- Ideal for large gaps
- Environmentally friendly solution that meets regulatory requirements

## MAIN PROPERTIES

TYPICAL PROPERTIES	VALUE	TEST METHOD
Composition	Two-part ceramic filled dispensable silicone gap filler	
Color	Part A:Pink Part B:White	Visual
Viscosity before combining	350,000 cP	ASTM D2196
Mix ratio	1:1	
Shelf Life	9 months	
PROPERTIES AFTER CURING		
Thermal Conductivity	3.6 W/mK	Hot Disk
Density	3.2 g/cc	Helium Pycnometer
Hardness (3sec)	69 Shore 00	ASTM D2240
Outgassing TML (weight)	0.58%	ASTM E595
Min. bond line thickness	85 µm	Laird lab
Operating Temperature Range	-55°C to 200°C	Laird Reliability Test
Rth at 1mm, 50°C, 50psi	0.437 °C-in <sup>2</sup> /W	ASTM D5470 (Modified)
Dielectric Breakdown Voltage at 1mm	9kV AC	ASTM D149
UL Flammability Rating	V-0	Laird LAB
Volume Resistivity	2.6 x 10 <sup>14</sup> ohm-cm	ISO 14309
Cure condition	1 hour@70°C, 0.5 hour@100°C	Laird LAB

American: +1.866.928.8181  
Europe: +44.8031.2460.0  
Asia: +86.755.2714.1166

[www.laird.com](http://www.laird.com)

THR-DS-Tflex™ CR350\_12.01.2020

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All information is subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user. Laird Technologies makes no warranties as to the fitness, merchantability, suitability or non-infringement of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies' Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2013 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trademarks or registered trademarks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights.


## PACKAGING

TYPE	FILL VOLUME	FILL WEIGHT
50cc duo-cartridge (2x25cc)	47cc	150g
400cc duo-cartridge (2x200cc)	387cc	1240g
1 gallon pail x2	4062cc x2	13kg x2
5 gallons pail x2	6250cc x2	20kg x2

## OPTIONS

Available with or without beads (8 mils and 10 mils beads)

## CURING PROFILE



The above cure profiles are guideline recommendations. Cure conditions (time and temperature) may vary based on customers' experience and their application requirements, as well as customer curing equipment, oven loading and actual oven temperatures.