

IEC Appliance Inlet with Filter, Fuseholder 1- or 2-pole, Line Switch 2-pole



Protection class I with shield



Protection class II without shield



See below:  
[Approvals and Compliances](#)

**Description**

- Panel mount :  
 Snap-in version front side
- 4 Functions :  
 Appliance Inlet protection class I or II , Line Switch 2-pole , Fuseholder for fuse-links 5 x 20 mm 1- or 2-pole , Line filter in standard and medical version
- Quick connect terminals 4.8 x 0.8 mm

**Unique Selling Proposition**

- Most compact solution on the market
- Innovative EMC-shielding
- Easy and flexible snap-in mounting
- Protection class I or II versions

**Characteristics**

- Ultra-compact design. Small dimensions in front of and behind the panel
- All single elements are already wired
- For added safety "Extra-Safe" fuse drawers are available
- Innovative EMC-shielding with flexible steel segments for an excellent contact
- Suitable for use in medical equipment according to IEC/UL 60601-1 (1 MOOP, 1 MOPP)  
 For applications according IEC/UL 62368-1 we recommend variants with bleed resistor

**Other versions on request**

- Fuse drawer 1-pole, plus spare fuse case
- Fuse drawer 2-pole, with shorting bar
- Other rocker marking

**References**

Alternative: version without line filter [KM](#)  
 Alternative: version for screw mounting [DD12](#)

**Weblinks**

[pdf data sheet](#), [html datasheet](#), [General Product Information](#), [Approvals](#), [Distributor-Stock-Check](#), [Accessories](#), [Detailed request for product](#)

**Technical Data**

|                                 |                                                                           |                                   |                                                                                                                                  |
|---------------------------------|---------------------------------------------------------------------------|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| Ratings IEC                     | 1 - 10A @ Ta 40 °C / 250VAC; 50Hz                                         | Appliance inlet/-outlet           | C14 C18 acc. to IEC 60320-1, UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 10A, Protection Class I or II |
| Ratings UL/CSA                  | 1 - 10A @ Ta 40 °C / 250VAC; 60Hz                                         | Fuseholder                        | 1-/2-pole, Shocksafe category PC2 acc. to IEC 60127-6, for fuse-links 5 x 20mm                                                   |
| Leakage Current                 | standard < 0.5mA (250V / 60Hz)<br>medical < 5 µA (250 V / 60 Hz)          | Rated Power Acceptance @ Ta 23 °C | 5 x 20: 2W (1 pole)/ 1.6W (2-pole) per pole                                                                                      |
| Dielectric Strength             | > 1.7kVDC between L-N<br>> 2.7kVDC between L/N-PE<br>Test voltage (2 sec) | Power Acceptance @ Ta > 23°C      | Admissible power acceptance at higher ambient temperature see derating curves                                                    |
| Allowable Operation Temperature | -25 °C to 85 °C                                                           | Line Switch                       | 2-pole, non-illuminated, acc. to IEC 61058-1<br><a href="#">Technical Details</a>                                                |
| Climatic Category               | 25/085/21 acc. to IEC 60068-1                                             | Line Filter                       | Standard and Medical Version, IEC 60939, UL 1283, CSA C22.2 no. 8<br><a href="#">Technical Details</a>                           |
| IP-Protection                   | front side IP40 acc. to IEC 60529                                         | MTBF                              | > 1'800'000h acc. to MIL-HB-217 F                                                                                                |
| Protection Class                | Suitable for appliances with protection class I or II acc. to IEC 61140   |                                   |                                                                                                                                  |
| Terminal                        | Quick connect terminals 4.8 x 0.8 mm                                      |                                   |                                                                                                                                  |
| Panel Thickness S               | Snap-in: 1/1.5/2/2.5 mm (all steps with one variant)                      |                                   |                                                                                                                                  |
| Material                        | Thermoplastic, black, UL 94V-0                                            |                                   |                                                                                                                                  |

**Approvals and Compliances**




Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

### Approvals









The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products.

Approval Reference Type: KMF

| Approval Logo                                                                    | Certificates                  | Certification Body | Description                                      |
|----------------------------------------------------------------------------------|-------------------------------|--------------------|--------------------------------------------------|
|  | <a href="#">VDE Approvals</a> | VDE                | Certificate Number: 40035743                     |
|  | <a href="#">UL Approvals</a>  | UL                 | UR File Number: E72928                           |
|  | <a href="#">CQC Approvals</a> | CQC                | CQC Certificate Number: 18001186843, 22001363976 |




### Product standards

Product standards that are referenced

| Organization                                                                       | Design                | Standard         | Description                                                           |
|------------------------------------------------------------------------------------|-----------------------|------------------|-----------------------------------------------------------------------|
|    | Designed according to | IEC 60320-1      | Appliance couplers for household and similar general purposes         |
|    | Designed according to | IEC 60939        | Passive filters for suppressing electromagnetic interference          |
|    | Designed according to | IEC 60127-6      | Miniature fuses. Part 6. Fuse-holders for miniature fuse-links        |
|  | Designed according to | IEC 61058-1      | Switches for appliances. Part 1. General requirements                 |
|  | Designed according to | UL 498           | Standard for Attachment Plugs and Receptacles                         |
|  | Designed according to | UL 1283          | Passive filters for suppressing electromagnetic interference          |
|  | Designed according to | CSA C22.2 no. 42 | General Use Receptacles, Attachment Plugs, and Similar Wiring Devices |
|  | Designed according to | CSA C22.2 no. 8  | Electromagnetic interference (EMI) filters                            |








### Application standards

Application standards where the product can be used

| Organization                                                                       | Design                         | Standard       | Description                                                                                                                                                                                                                  |
|------------------------------------------------------------------------------------|--------------------------------|----------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | Suitable for applications acc. | IEC/UL 62368-1 | Audio/video, information and communication technology equipment - Part 1: Safety requirements                                                                                                                                |
|  | Suitable for applications acc. | IEC 60601-1    | Medical electrical equipment - Part 1: General requirements for basic safety and essential performance                                                                                                                       |
|  | Suitable for applications acc. | IEC 60335-1    | Safety of electrical appliances for household and similar purposes. Meets the requirements for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 & -13. |


### Compliances

The product complies with following Guide Lines


| Identification                                                                    | Details                                        | Initiator   | Description                                                                                                                                                                                           |
|-----------------------------------------------------------------------------------|------------------------------------------------|-------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | <a href="#">CE declaration of conformity</a>   | SCHURTER AG | The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008. |
|  | <a href="#">UKCA declaration of conformity</a> | SCHURTER AG | The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.                                                  |
|  | RoHS                                           | SCHURTER AG | Directive RoHS 2011/65/EU, Amendment (EU) 2015/863                                                                                                                                                    |
|  | China RoHS                                     | SCHURTER AG | The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.                                                                                  |
|  | REACH                                          | SCHURTER AG | On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.                               |
|  | White Paper Glow wire test                     | SCHURTER AG | Meets the requirements of IEC 60335-1 for appliances in unattended use. This includes the enhanced requirements of glow wire tests acc. to IEC 60695-2-11 or -12 & -13.                               |
|  | Medical Equipment                              | SCHURTER AG | Suitable for use in medical equipment according to IEC/UL 60601-1 (1 MOPP, 1 MOPP)                                                                                                                    |

### Dimensions [mm]

With shield



Without shield




**Technical Data of Filter-Components**

| Rated Current [A] | Filter-Type                          | Inductances L [mH] | Capacitance CX [nF] | Capacitance CY [nF] | R [MΩ] |
|-------------------|--------------------------------------|--------------------|---------------------|---------------------|--------|
| 1                 | Standard version                     | 2 x 11             | 47                  | 2.2                 | -      |
| 2                 | Standard version                     | 2 x 4              | 47                  | 2.2                 | -      |
| 4                 | Standard version                     | 2 x 1.6            | 47                  | 2.2                 | -      |
| 6                 | Standard version                     | 2 x 0.7            | 47                  | 2.2                 | -      |
| 10                | Standard version                     | 2 x 0.4            | 47                  | 2.2                 | -      |
| 2                 | Standard Version with Bleed Resistor | 2 x 4              | 47                  | 2.2                 | -      |
| 10                | Standard Version with Bleed Resistor | 2 x 0.4            | 47                  | 2.2                 | -      |
| 1                 | Medical Version (M5)                 | 2 x 11             | 47                  | -                   | 1      |
| 2                 | Medical Version (M5)                 | 2 x 4              | 47                  | -                   | 1      |
| 4                 | Medical Version (M5)                 | 2 x 1.6            | 47                  | -                   | 1      |
| 6                 | Medical Version (M5)                 | 2 x 0.7            | 47                  | -                   | 1      |
| 10                | Medical Version (M5)                 | 2 x 0.4            | 47                  | -                   | 1      |


Diagrams

Standard version




- 1) Line
- 2) Load

Medical Version (M5)



- 1) Line
- 2) Load


Medicalversion (M5), Protection Class II




- 1) Line
- 2) Load

Derating Curves

1-pole



2-pole




Attenuation Loss


----- 50Ω differential mode    \_\_\_\_ 50Ω common mode

Standard version


1 A




2 A




4 A



6 A




10 A




Medical version (M5)


1 A




2 A




4 A



6 A



10 A



All Variants

| Rated Current [A] | Filter-Type                          | Fuseholder | Line Switch | Protection Class | Shield | Order Number |
|-------------------|--------------------------------------|------------|-------------|------------------|--------|--------------|
| 1                 | Standard version                     | 1-pole     | 2-pole      | I                | ●      | KMF1.1211.11 |
| 2                 | Standard version                     | 1-pole     | 2-pole      | I                | ●      | KMF1.1221.11 |
| 4                 | Standard version                     | 1-pole     | 2-pole      | I                | ●      | KMF1.1241.11 |
| 6                 | Standard version                     | 1-pole     | 2-pole      | I                | ●      | KMF1.1261.11 |
| 10                | Standard version                     | 1-pole     | 2-pole      | I                | ●      | KMF1.1291.11 |
| 1                 | Standard version                     | 2-pole     | 2-pole      | I                | ●      | KMF1.1111.11 |
| 2                 | Standard version                     | 2-pole     | 2-pole      | I                | ●      | KMF1.1121.11 |
| 4                 | Standard version                     | 2-pole     | 2-pole      | I                | ●      | KMF1.1141.11 |
| 6                 | Standard version                     | 2-pole     | 2-pole      | I                | ●      | KMF1.1161.11 |
| 10                | Standard version                     | 2-pole     | 2-pole      | I                | ●      | KMF1.1191.11 |
| 10                | Standard Version with Bleed Resistor | 1-pole     | 2-pole      | I                | ●      | 3-134-743    |
| 2                 | Standard Version with Bleed Resistor | 2-pole     | 2-pole      | I                | ●      | 3-122-687    |
| 1                 | Medical Version (M5)                 | 1-pole     | 2-pole      | I                | ●      | KMF1.1213.11 |
| 2                 | Medical Version (M5)                 | 1-pole     | 2-pole      | I                | ●      | KMF1.1223.11 |
| 4                 | Medical Version (M5)                 | 1-pole     | 2-pole      | I                | ●      | KMF1.1243.11 |
| 6                 | Medical Version (M5)                 | 1-pole     | 2-pole      | I                | ●      | KMF1.1263.11 |
| 10                | Medical Version (M5)                 | 1-pole     | 2-pole      | II               |        | KMF0.2293.11 |
| 10                | Medical Version (M5)                 | 1-pole     | 2-pole      | I                | ●      | KMF1.1293.11 |
| 1                 | Medical Version (M5)                 | 2-pole     | 2-pole      | II               |        | KMF0.2113.11 |
| 1                 | Medical Version (M5)                 | 2-pole     | 2-pole      | I                | ●      | KMF1.1113.11 |
| 2                 | Medical Version (M5)                 | 2-pole     | 2-pole      | II               |        | KMF0.2123.11 |
| 2                 | Medical Version (M5)                 | 2-pole     | 2-pole      | I                | ●      | KMF1.1123.11 |
| 4                 | Medical Version (M5)                 | 2-pole     | 2-pole      | II               |        | KMF0.2143.11 |
| 4                 | Medical Version (M5)                 | 2-pole     | 2-pole      | I                | ●      | KMF1.1143.11 |
| 6                 | Medical Version (M5)                 | 2-pole     | 2-pole      | II               |        | KMF0.2163.11 |
| 6                 | Medical Version (M5)                 | 2-pole     | 2-pole      | I                | ●      | KMF1.1163.11 |
| 10                | Medical Version (M5)                 | 2-pole     | 2-pole      | I                |        | 3-127-408    |
| 10                | Medical Version (M5)                 | 2-pole     | 2-pole      | II               |        | KMF0.2193.11 |
| 10                | Medical Version (M5)                 | 2-pole     | 2-pole      | I                | ●      | KMF1.1193.11 |

Most Popular.


Availability for all products can be searched real-time: <https://www.schurter.com/en/info-center/support-tools/stock-check-distributors>

The fuse drawer is not included and must be ordered separately (see required accessory).





Packaging unit

20 Pcs


### Required Accessory

|                                                                                   |                                                                                                            | Description |
|-----------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------|-------------|
|  | <a href="#">Fusedrawer_2</a><br>Fusedrawer for Fuse Links 5x20 mm, with or without Voltage Selector Insert |             |
|                                                                                   | Fingergrip, 2-pole                                                                                         | 4301.1401   |
|                                                                                   | Extra-Safe, 2-pole                                                                                         | 4301.1403   |
|                                                                                   | Fingergrip, 1-pole                                                                                         | 4301.1405   |
|                                                                                   | Extra-Safe, 1-pole                                                                                         | 4301.1407   |
|                                                                                   |                                                                                                            | ...         |

### Accessories

|                                                                                     |                                                                     |           |
|-------------------------------------------------------------------------------------|---------------------------------------------------------------------|-----------|
|    | <a href="#">Wire_Harness</a><br>Wire harness for SCHURTER products  |           |
|                                                                                     |                                                                     |           |
|   | <a href="#">Assorted_Covers</a><br>Rear Cover                       |           |
|                                                                                     | 0859.0076                                                           |           |
|  | <a href="#">RC320</a><br>Rear Cover for Power Entry Module          |           |
|                                                                                     |                                                                     |           |
|  | <a href="#">Cord_retaining_kits</a><br>Cord retaining strain relief |           |
|                                                                                     | Flat head, A                                                        | 4700.0001 |

### Mating Outlets/Connectors

|                                                                                     |                                                                                                                                      | Category / Description |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|------------------------|
|  | <a href="#">Appliance Outlet Overview complete</a>                                                                                   |                        |
|                                                                                     | 4787, Mounting: Screw-on mounting, Appliance Outlet: IEC Solder terminals, 10 A, Suitable for appliances with protection class I     | 4787                   |
|                                                                                     | 4788, Mounting: Snap-in version, Appliance Outlet: IEC Solder / Quick Connect, 10 A, Suitable for appliances with protection class I | 4788                   |
|                                                                                     | IEC Appliance Outlet F or H, Screw-on Mounting, Front Side, Solder, PCB or Quick-connect Terminal                                    | 5091                   |

Connector Overview complete



|                                                                                             |         |
|---------------------------------------------------------------------------------------------|---------|
| 4782 Mounting: Power Cord, 3 x 1 mm <sup>2</sup> / 3 x 18 AWG, Cable, Connector: IEC C13    | 4782    |
| 4785 Mounting: Power Cord, 3 x 1 mm <sup>2</sup> / 3 x 18 AWG, Cable, Connector: IEC C13    | 4785    |
| 4300-06 Mounting: Power Cord, 3 x 1 mm <sup>2</sup> / 3 x 18 AWG, Cable, Connector: IEC C13 | 4300-06 |
| 4781 Mounting: Power Cord, Cable, Connector: IEC C15                                        | 4781    |
| 4784 Mounting: Power Cord, 3 x 1 mm <sup>2</sup> / 3 x 18 AWG, Cable, Connector: IEC C15    | 4784    |